

# Product data sheet

Specifications



## Push-to-test pilot light, Harmony 9001K, metal, polycarbonate, fresnel, red, 30mm, 120V

9001KT38R31

⚠ Discontinued on: Mar 31, 2023

⚠ End-of-service on: Apr 15, 2023

⚠ Discontinued

### Main

Range Of Product	Harmony 9001K
Product Or Component Type	Push-to-test pilot light
Device Short Name	K

### Complementary

Bezel Material	Metal
Mounting Diameter	30 mm
Lens Type	Fresnel plastic
Cap/Operator Or Lens Colour	Red
Bulb Base	BA 9s
Light Block Supply	Full voltage 120 V
Shape Of Screw Head	Round
Light Source	Incandescent bulb
Operating Mode	Push-to-test
Lens Type	Fresnel
[Us] Rated Supply Voltage	120 V
Light Block Supply	Full voltage or resistor
Contacts Type And Composition	1 C/O
Lens Material	Polycarbonate
Size	30 mm

### Environment

Product Certifications	CE UL listed file E42259 CCN NKCR CSA LR25490 class 3211 03
Nema Degree Of Protection	NEMA 1/2/3/3R/4/6/12/13

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	12.903 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Width	5.08 cm
Package 1 Length	32.774 cm
Package 1 Weight	181.437 g

# Sustainability

**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.


[Learn more about Green Premium >](#)


[Guide to assess a product’s sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

 Mercury Free

 Rohs Exemption Information   [Yes](#)

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	<a href="#">China RoHS declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations <a href="#">Circularity Profile</a>
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="#">www.P65Warnings.ca.gov</a>