

Product data sheet

Specifications



250V Illuminated "PLEASE CLEAN UP" Symbol 1M Sized Module, Bronze

8430SPCU_BZ

 **Discontinued on:** Jun 30, 2023

 **Discontinued**

Main

Range	ZENcelo
Product Or Component Type	Message indicator
Local Signalling	Please clean up: indicator light, LED (green)
Colour Tint	Bronze

Complementary

Clamping Connection Capacity	1 x 1...4 x 1 mm ² for solid stranded cable(s) 1 x 1.5...5 x 1.5 mm ² for solid stranded cable(s) 1 x 2.5...3 x 2.5 mm ² for solid stranded cable(s) 1 x 4...2 x 4 mm ² for solid stranded cable(s)
[Ue] Rated Operational Voltage	250 V AC 50/60 Hz
Material	Brass: metal parts Polycarbonate: base Polycarbonate: cover Polycarbonate: lenses
Connections - Terminals	Folded terminal
Width	23.2 mm
Height	45.8 mm
Depth	31.7 mm

Environment

Ambient Air Temperature For Operation	-5...45 °C
Ambient Air Temperature For Storage	0...60 °C
Relative Humidity	0...95 %
Environmental Characteristic	UV resistant
Operating Altitude	<= 2000 m
Ip Degree Of Protection	IP20

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.173 cm
Package 1 Width	2.325 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Length	4.58 cm
Package 1 Weight	19.7 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	24
Package 2 Height	10 cm
Package 2 Width	15.5 cm
Package 2 Length	24 cm
Package 2 Weight	516 g
Unit Type Of Package 3	CAR
Number Of Units In Package 3	240
Package 3 Height	16.5 cm
Package 3 Width	21 cm
Package 3 Length	40 cm
Package 3 Weight	4954 g

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations