

# Product data sheet

Specifications

## Cat.5e Patch Cord FTP 1M CM, Blue



ACTPC5ESBCM10BU

⚠ Discontinued on: Dec 15, 2021

⚠ Discontinued

### Main

Range	Actassi
Product	Patch cord
Colour	Blue
Cable Shielding Type	FTP

### Complementary

Type Of Cable	4 pair cables
Rated Voltage	150 V AC
[In] Rated Current	1.5 A
Insulation Resistance	1 MOhm
Length (Customizable Value In Configurator)	0...1 m
Communication Network Category	5e
Contacts Material	Phosphor bronze with 50 micro-inches gold over 100 micro-inches nickel
Contact Resistance	10 mOhm
Awg Gauge	AWG 26
Minimum Number Of Matings	1000 cycles
Targeted Region	Asia Pacific.

### Environment

Flame Retardance	CM
Standards	IEC 60603-7 FCC part 68 Subpart F AS/NZS 3080:2003

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.008 cm
Package 1 Width	21 cm
Package 1 Length	30.2 cm
Package 1 Weight	75 g

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

# Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

## Well-being performance

<div><div>✓</div></div>	Reach Free Of Svhc	
<div><div>✓</div></div>	Toxic Heavy Metal Free	
<div><div>✓</div></div>	Mercury Free	
<div><div>✓</div></div>	Rohs Exemption Information	Yes
Reach Regulation	<a href="#">REACH Declaration</a>	
Eu Rohs Directive	Compliant <a href="#">EU RoHS Declaration</a>	
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)	
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins	
Circularity Profile	No need of specific recycling operations	