


Product data sheet

Specifications

Cable duct - 25 x 25 mm - without cover - grey



AK2GD2525

Main

Product Or Component Type	Cable duct
Accessory / Separate Part Category	Cabling accessories
Range Compatibility	Spacial S3D Spacial CRN Thalassa PLA Thalassa PLS Thalassa PLM
Device Composition	Without cover
Quantity Per Set	Set of 8

Complementary

Colour	Grey (RAL 7030)
Fixing Mode	Clip-on support By screws
Material	PVC (polyvinyl chloride)
Height	25 mm
Length	2000 mm
Width	25 mm
Net Weight	0.26 kg
Total Number Of Wires	25

Environment

Ambient Air Temperature For Operation	-5...60 °C
Flame Retardance	V-0 conforming to UL 94
Fire Resistance	960 °C conforming to IEC 60695-2-1/1
Standards	VDE 0660 VDE 0506 DIN 43659

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.000 cm
Package 1 Width	2.500 cm
Package 1 Length	200.000 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Weight	207.000 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	8
Package 2 Height	4.500 cm
Package 2 Width	5.500 cm
Package 2 Length	200.500 cm
Package 2 Weight	1.877 kg
Unit Type Of Package 3	P2M
Number Of Units In Package 3	176
Package 3 Height	45.000 cm
Package 3 Width	200.000 cm
Package 3 Length	120.000 cm
Package 3 Weight	51.432 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability





Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

Well-being performance

	Reach Free Of Svhc	
	Toxic Heavy Metal Free	
	Mercury Free	
	Rohs Exemption Information	Yes
Reach Regulation		REACH Declaration
Eu Rohs Directive		Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation		China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)