


Product data sheet

Specifications

Cable duct - 50 x 75 mm - without cover - grey



AK2GD7550

Main

Product Or Component Type	Cable duct
Accessory / Separate Part Category	Cabling accessories
Range Compatibility	Spacial S3D Spacial CRN Thalassa PLA Thalassa PLS Thalassa PLM
Device Composition	Without cover
Quantity Per Set	Set of 8

Complementary

Colour	Grey (RAL 7030)
Fixing Mode	Clip-on support By screws
Material	PVC (polyvinyl chloride)
Height	50 mm
Length	2000 mm
Width	75 mm
Net Weight	0.88 kg
Total Number Of Wires	250

Environment

Ambient Air Temperature For Operation	-5...60 °C
Flame Retardance	V-0 conforming to UL 94
Fire Resistance	960 °C conforming to IEC 60695-2-1/1
Standards	DIN 43659 VDE 0660 VDE 0506

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	9.5 cm
Package 1 Width	17.0 cm
Package 1 Length	200.0 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Weight	689.9 g
Unit Type Of Package 2	PAL
Number Of Units In Package 2	200
Package 2 Height	77.0 cm
Package 2 Width	280.0 cm
Package 2 Length	120.0 cm
Package 2 Weight	163.0 kg
Unit Type Of Package 3	CAR
Number Of Units In Package 3	8
Package 3 Height	9.5 cm
Package 3 Width	17.0 cm
Package 3 Length	200.0 cm
Package 3 Weight	5.52 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

	Reach Free Of Svhc	
	Toxic Heavy Metal Free	
	Mercury Free	
	Rohs Exemption Information	Yes
Reach Regulation		REACH Declaration
Eu Rohs Directive		Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation		China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)