

# Product data sheet

Specifications



## Multifix Plus - apparatus box - 2 x 3 gangs - without cover - 67x40mm

ALB71338

⚠ Discontinued on: Jun 30, 2023

⚠ Discontinued

### Main

Range Of Product	Multifix
Range	Multifix
Product Name	Multifix Plus
Product Or Component Type	Apparatus box
Device Presentation	Without cover
Quantity Per Set	Set of 6

### Complementary

Function Available	Anti-rotation system
Number Of Gangs	2 x 3 gangs
Fixing Mode	By screws and claws
Material	PS (polystyrene)
Mechanical Robustness	Fire resistance
Colour Tint	Box: blue (RAL 5015)
Cable Entry	6 knock-out
Distance Between Centers	57 mm
Height	155 mm
Width	142 mm
Depth	40 mm
Connections - Terminals	Screwed
Tube Diameter	0.84 mm
Internal Depth	38 mm
Length	165 mm
Maximum Cable Cross Section	2.5 mm <sup>2</sup>
Sealing	Without
Surface Treatment	Untreated

### Environment

Ambient Air Temperature For Operation	-5...60 °C
Ip Degree Of Protection	IP20

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Standards	IEC 60670-1
-----------	-------------

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4 cm
Package 1 Width	15.5 cm
Package 1 Length	17.5 cm
Package 1 Weight	76 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	6
Package 2 Height	15 cm
Package 2 Width	20.8 cm
Package 2 Length	37.5 cm
Package 2 Weight	650 g
Unit Type Of Package 3	S04
Number Of Units In Package 3	18
Package 3 Height	30 cm
Package 3 Width	40 cm
Package 3 Length	60 cm
Package 3 Weight	2.815 kg

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information   Yes

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations