

Product data sheet

Specifications



Acti9 centralized control iATLc

A9C15404

Main

Range Of Product	Acti9
Device Short Name	iATLc
Product Or Component Type	Centralized control auxiliary
[Uc] Control Circuit Voltage	24...240 V AC 50/60 Hz impulse

Complementary

[Ui] Rated Insulation Voltage	440 V
[Uimp] Rated Impulse Withstand Voltage	4 kV
Remote Control Type	2 entries for switch
Mounting Mode	Fixed, on right side of TL
Mounting Support	DIN rail
9 Mm Pitches	1
Height	81 mm
Width	9 mm
Depth	69 mm
Colour	White
Connections - Terminals	Tunnel type terminals0.5...4 mm² - rigid Tunnel type terminals0.5...4 mm² - rigid - with cable end Tunnel type terminals1...4 mm² - flexible Tunnel type terminals1...4 mm² - flexible - with cable end
Wire Stripping Length	11 mm
Tightening Torque	1 N.m
Range Compatibility	Acti 9 Acti9 iTL iTL Acti 9 Acti9 iTL iTLi Acti 9 Acti9 iTL iTLs
Product Compatibility	ITL (32 A) ITL (16 A)

Environment

Overvoltage Category	III
Ip Degree Of Protection	IP20 conforming to IEC 60529
Tropicalisation	2
Relative Humidity	95 % at 55 °C
Ambient Air Temperature For Operation	-20...50 °C

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Ambient Air Temperature For Storage	-40...70 °C
Standards	EN/IEC 60669-2-2

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8 cm
Package 1 Width	2.4 cm
Package 1 Length	9.4 cm
Package 1 Weight	40 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	12
Package 2 Height	8.5 cm
Package 2 Width	9.5 cm
Package 2 Length	26.5 cm
Package 2 Weight	534 g
Unit Type Of Package 3	S03
Number Of Units In Package 3	108
Package 3 Height	30 cm
Package 3 Width	30 cm
Package 3 Length	40 cm
Package 3 Weight	4.76 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

✓ Halogen Free Plastic Parts Product

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations