

Product data sheet

Specifications



MX Shunt Trip MX plus 1 OF 24Vac dc

A9N26948

Main

Range Of Product	Acti9
Product Or Component Type	Shunt trip release with OC contact
Device Short Name	MX + OF
Signal Contacts Composition	1 C/O
[Uc] Control Circuit Voltage	12...24 V AC 50/60 Hz 12...24 V DC
9 Mm Pitches	2

Complementary

Range Compatibility	Acti 9 Acti9 iDPN Acti 9 Acti9 C120 Acti 9 Acti9 C40 Acti 9 Acti9 C60H-DC Acti 9 Acti9 C60NA-DC Acti 9 Acti9 C60PV-DC Acti 9 Acti9 DPN Vigi Acti 9 Acti9 DT40 Acti 9 Acti9 DT60 Acti 9 Acti9 ID C40 Acti 9 Acti9 IDc Acti 9 Acti9 ITG40 Acti 9 Acti9 ID Acti 9 Acti9 DPN
Local Signalling	Action indicator
Mounting Mode	Fixed
Mounting Support	35 mm symmetrical DIN rail
Comb Busbar And Distribution Block Compatibility	Top: YES
Height	82.5 mm
Width	18 mm
Depth	73.5 mm
Net Weight	65 g
Colour	White
Connections - Terminals	Clamp terminal - 1 cable(s) 2.5 mm ² - flexible
Wire Stripping Length	9 mm
Tightening Torque	1 N.m
Compatibility Code	MX + OF

Environment

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Standards	EN/IEC 60947-1 UL 489 UL 1077 C22.2 No. 5 C22.2 No. 235 GB/T 14048.5
Product Certifications	ASTA LCIE KEMA ASEFA
Tropicalisation	2 conforming to EN/IEC 60947-5-1
Relative Humidity	95 % at 55 °C
Ambient Air Temperature For Operation	-25...50 °C
Ambient Air Temperature For Storage	-40...85 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8 cm
Package 1 Width	3 cm
Package 1 Length	9.3 cm
Package 1 Weight	74 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	8
Package 2 Height	8.7 cm
Package 2 Width	10 cm
Package 2 Length	26.5 cm
Package 2 Weight	652 g
Unit Type Of Package 3	S03
Number Of Units In Package 3	72
Package 3 Height	30 cm
Package 3 Width	30 cm
Package 3 Length	40 cm
Package 3 Weight	6.363 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information