

Product data sheet

Specifications



Multifix Plus - apparatus box - 2 gangs - without cover - 67x50mm

ALB71335

⚠ Discontinued on: Mar 31, 2021

⚠ Discontinued

Main

Range Of Product	Multifix
Range	Multifix
Product Name	Multifix Plus
Product Or Component Type	Apparatus box
Device Presentation	Without cover
Quantity Per Set	Set of 10

Complementary

Function Available	Anti-rotation system
Number Of Gangs	2 gangs
Installation Direction	Horizontal
Fixing Mode	By screws and claws
Material	PS (polystyrene)
Mechanical Robustness	Fire resistance
Colour Tint	Box: blue (RAL 5015)
Cable Entry	6 knock-out
Distance Between Centers	71 mm
Height	71 mm
Width	71 mm
Depth	50 mm
Connections - Terminals	Screwed
Diameter	67 mm
Distance Between Supports	60 mm
Tube Diameter	0.84 mm
Internal Depth	38 mm
Length	142 mm
Maximum Cable Cross Section	2.5 mm ²
Sealing	Without
Surface Treatment	Untreated

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Environment

Ambient Air Temperature For Operation	-5...60 °C
Ip Degree Of Protection	IP20
Standards	IEC 60670-1

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	21.5 cm
Package 1 Width	4.9 cm
Package 1 Length	7.1 cm
Package 1 Weight	62 g

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations