

# Product data sheet

Specifications



## NetShelter SV 48U 600mm Wide x 1200mm Deep Enclosure with Sides Black

AR2507

### Overview

Presentation	Deep and Tall Universal IT Enclosure for low to medium density server and networking applications that either require additional equipment clearance space or more open space for ease of access in the rear of the enclosure. Tall to provide 48U spaces for environments that can take advantage of higher spaces and provide more mounting u-spaces at each enclosure footprint. Compact width to optimize data center space.
Lead Time	Usually in Stock

### Main

Number Of Rack Unit	48U
Provided Equipment	Baying hardware Doors Key(s) Keyed-alike doors and side panels Leveling feet Mounting hardware Pre-installed casters 4 x bolt down brackets Roof Side panels Unpacking sheet

### Physical

Height	232.4 cm
Width	60 cm
Depth	120 cm
Net Weight	131.2 kg
Colour	Black
Mounting Preference	No preference
Mounting Mode	Not rack-mountable
Maximum Mounting Depth	91.69 cm
Minimum Mounting Depth	16.76 cm
Rack Width	19"
Marking	14 gauge EIA mounting rail 16 gauge front door 18 gauge post 16 gauge rear door 19 gauge roof 18 gauge side panels
Permanent Permissible Load	459.94 kg dynamic 1000.17 kg static

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

## Conformance

Standards	UL 2416 UL 60950-1 EIA-310E
-----------	-----------------------------------

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	244.8 cm
Package 1 Width	70 cm
Package 1 Length	130 cm
Package 1 Weight	151.382 kg

## Contractual warranty

Warranty	5 year repair or replace
----------	--------------------------

## Sustainability

**Green Premium™** label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Take-back   Transparency   RoHS/REACH

## Resource performance

✓ Take-Back Program Available

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information   [Yes](#)

## Certifications & Standards

Reach Regulation   [REACH Declaration](#)

Eu Rohs Directive   Pro-active compliance (Product out of EU RoHS legal scope)  
[EU RoHS Declaration](#)

Environmental Disclosure   [Product Environmental Profile](#)