


Product data sheet

Specifications



APC Replacement Battery Cartridge, VRLA, 9Ah, 72V DC, 2-year warranty

APCRBCV205

Overview

Lead Time	Usually in Stock
-----------	------------------

Main

Product Or Component Type	Replacement battery cartridge
Number Of Rack Unit	0U
Battery Type	VRLA

Batteries & Runtime

Battery Location	Internal battery
Number Of Battery Blocks Per String	6
Number Of Battery Free Slots	0
Number Of Battery Filled Slots	0
Battery Voltage	72 V
Number Of Battery Replacement Quantity	1

Physical

Height	64.8 mm
Width	150.9 mm
Depth	98.6 mm
Net Weight	15 kg
Mounting Mode	Not rack-mountable
Usb Compatible	No

Output

Battery Capacity	9 Ah
------------------	------

Conformance

Product Certifications	CB
------------------------	----

Environmental

Ambient Air Temperature For Operation	0...40 °C
Operating Altitude	0...2000 m

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Relative Humidity	0...90 % non-condensing
Ambient Air Temperature For Storage	-15...45 °C
Storage Altitude	0...3000 m
Storage Relative Humidity	0...95 % non-condensing

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	30.000 cm
Package 1 Width	36.500 cm
Package 1 Length	44.000 cm
Package 1 Weight	17.106 kg
Unit Type Of Package 2	P12
Number Of Units In Package 2	6
Package 2 Height	49.000 cm
Package 2 Width	80.000 cm
Package 2 Length	120.000 cm
Package 2 Weight	115.000 kg

Contractual warranty

Warranty	2 Years
----------	---------

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information