

# Product data sheet

Specifications



## Easy UPS On-Line SRVS Network Management Card, with direct SNMP connection

APVS9601

⚠ Discontinued on: Aug 31, 2023

⚠ To be end-of-service on: Aug 31, 2024

⚠ Discontinued - Service only

### Overview

Presentation	Network management card that remotely monitors and controls Schneider Electric Easy UPS. UPS management accessory that provides contact closures for remote monitoring.
Lead Time	Usually in Stock

### Main

Product Or Component Type	UPS network management cards
Communication Port Protocol	TCP/IP SNMP v1 SNMP v2 SNMP v3 UDP (User Datagram Protocol)
Provided Equipment	CD with software User manual
Range Of Product	Easy UPS 1Ph Management Accessory Cards & Management Software

### Complementary

Physical Interface	1 Ethernet port 10/100BASE-T, transmission rate: 10/100 Mbit/s RJ45
Local Signalling	LED (green) for port communication at 100 Mbps LED (yellow) for port communication at 10 Mbps

### Environment

Ambient Air Temperature For Operation	0...40 °C
Ambient Air Temperature For Storage	-15...45 °C
Relative Humidity	0...95 % non-condensing

### Physical

Height	1.5 cm
Width	4.7 cm
Depth	2.3 cm
Net Weight	0.11 kg
Mounting Mode	-

### Packing Units

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.400 cm
Package 1 Width	13.500 cm
Package 1 Length	16.900 cm
Package 1 Weight	130.700 g
Unit Type Of Package 2	S04
Number Of Units In Package 2	56
Package 2 Height	30.000 cm
Package 2 Width	40.000 cm
Package 2 Length	60.000 cm
Package 2 Weight	7.954 kg
Unit Type Of Package 3	P06
Number Of Units In Package 3	224
Package 3 Height	75.000 cm
Package 3 Width	80.000 cm
Package 3 Length	60.000 cm
Package 3 Weight	39.817 kg

## Contractual warranty

Warranty	1 year
----------	--------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

 Rohs Exemption Information   [Yes](#)

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins