

Product data sheet

Specifications



NFC cartridge fuses, TeSys GS, cylindrical, 22mm x 58mm, fuse type aM, 690VAC, 40A, without striker, set of 10 parts

DF2FA40

Main

Range Of Product	TeSys fuse-disconnector
Product Or Component Type	Cartridge fuse
Device Short Name	DF2
[Ue] Rated Operational Voltage	690 V AC
Fuse Size	22 x 58 mm
Fuse Type	NFC
Quantity Per Set	Set of 10

Complementary

[In] Rated Current	40 A 690 V
Fuse Curve	AM
Net Weight	0.045 kg

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.4 cm
Package 1 Width	11.8 cm
Package 1 Length	12.0 cm
Package 1 Weight	49.0 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	2.4 cm
Package 2 Width	11.8 cm
Package 2 Length	12.0 cm
Package 2 Weight	494.0 g
Unit Type Of Package 3	S01
Number Of Units In Package 3	120
Package 3 Height	15.0 cm
Package 3 Width	15.0 cm
Package 3 Length	40.0 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 3 Weight	6.62 kg
------------------	---------

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

<div><div>✓</div></div>	Reach Free Of Svhc	
<div><div>✓</div></div>	Toxic Heavy Metal Free	
<div><div>✓</div></div>	Mercury Free	
<div><div>✓</div></div>	Rohs Exemption Information	Yes
<div><div>✓</div></div>	Pvc Free	
Reach Regulation	REACH Declaration	
Eu Rohs Directive	Compliant EU RoHS Declaration	
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)	
California Proposition 65	WARNING: Cancer and Reproductive Harm - www.P65Warnings.ca.gov	