

# Product data sheet

Specifications



Switched socket, AvatarOn, LED, screw terminal, IP20, white

E8315\_15\_WE\_G2

## Main

Product Or Component Type	Switched socket
Device Application	Power supply
Device Presentation	Complete product
Outlet Poles Configuration	3P with shutter
Type Of Packing	Flow-pack

## Complementary

Rated Current	15 A socket-outlet
[Ue] Rated Operational Voltage	250 V AC 50/60 Hz
Socket Number	1
Outlet Standard Description	With earthing contact
Outlet Standard	British BS 546
Number Of Gangs	1 gang
Pilot Light	LED
Service Life In Cycles	20000 cycles
Electrical Durability	5000 cycles
Connections - Terminals	Screw terminal
Material	Polycarbonate: grid plate Polycarbonate: surround
Surface Finish	Glossy
Surface Treatment	Painted cover plate
Device Mounting	Surface
Fixing Mode	Screw
Height	86 mm
Width	86 mm
Depth	32.6 mm

## Environment

Ip Degree Of Protection	IP20
Ambient Air Temperature For Operation	-5...45 °C
Ambient Air Temperature For Storage	-5...60 °C

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Standards	MS 1577 SS 472 BS 546
Product Certifications	SIRIM

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.2 cm
Package 1 Width	8.6 cm
Package 1 Length	8.6 cm
Package 1 Weight	91.0 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	9.5 cm
Package 2 Width	19.0 cm
Package 2 Length	19.5 cm
Package 2 Weight	955.0 g
Unit Type Of Package 3	CAR
Number Of Units In Package 3	60
Package 3 Height	21.0 cm
Package 3 Width	30.0 cm
Package 3 Length	39.5 cm
Package 3 Weight	6230.0 g

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information   Yes

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations