

# Product data sheet

Specifications



## Easy UPS 3M Classic Battery Cabinet with batteries, IEC, 1000mm wide - Config C

E3MCBC10C

### Overview

|              |  |
|--------------|--|
| Presentation | Battery cabinet that includes batteries and battery breaker. |
| Lead Time    | Usually Ships within 6 Weeks                                 |

### Main

|                           |                    |
|---------------------------|--------------------|
| Product Or Component Type | Battery cabinet    |
| Battery Type              | VRLA               |
| Provided Equipment        | Installation guide |

### Batteries & Runtime

|                                |                          |
|--------------------------------|--------------------------|
| Number Of Battery Free Slots   | 0                        |
| Number Of Battery Filled Slots | 0                        |
| Device Mounting                | Enclosed battery cabinet |

### Physical

|               |                    |
|---------------|--------------------|
| Height        | 189.5 cm           |
| Width         | 100.2 cm           |
| Depth         | 84.5 cm            |
| Net Weight    | 1404 kg            |
| Mounting Mode | Not rack-mountable |

### Environmental

|                                       |             |
|---------------------------------------|-------------|
| Ambient Air Temperature For Operation | 0...40 °C   |
| Ambient Air Temperature For Storage   | -15...40 °C |

### Packing Units

|                              |         |
|------------------------------|---------|
| Unit Type Of Package 1       | PCE     |
| Number Of Units In Package 1 | 1       |
| Package 1 Height             | 198 cm  |
| Package 1 Width              | 97 cm   |
| Package 1 Length             | 113 cm  |
| Package 1 Weight             | 1424 kg |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

# Sustainability

**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.


[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

 Rohs Exemption Information   [Yes](#)

## Certifications & Standards

|                          |   |
|--------------------------|---|
| Reach Regulation         | <a href="#">REACH Declaration</a>   |
| Eu Rohs Directive        | Compliant with Exemptions   |
| China Rohs Regulation    | <a href="#">China RoHS declaration</a><br>Product out of China RoHS scope. Substance declaration for your information |
| Environmental Disclosure | <a href="#">Product Environmental Profile</a>   |
| Circularity Profile      | <a href="#">End of Life Information</a>   |