

# Product data sheet

Specifications



## Asfora, TV-SAT individual socket, 1dB, white

EPH3400421

### Main

Range	Asfora
Product Or Component Type	TV/SAT socket
Device Presentation	Complete product
Tv Socket Type	Individual socket
Wiring Device Additional Information	For parallel distribution systems
Type Of Packing	Flow-pack

### Complementary

Device Mounting	Flush
Fixing Mode	Claws51...80 mm
Socket Number	2
Tv Connector	Male IEC 9.52 mm
Sat Connector	F type
Attenuation	1 dB
Colour Tint	White
Surface Finish	Glossy
Material	ABS (acrylonitrile butadiene-styrene): central plate ABS (acrylonitrile butadiene-styrene): cover frame
Dc Current Flow	In SAT socket
Number Per Line	1
Connections - Terminals	Screwless terminals
Conductor Material	Copper
Height	83 mm
Width	83 mm
Depth	42 mm
Projecting Depth	13 mm
Net Weight	0.117 kg
Ip Degree Of Protection	IP20

### Environment

Quality Labels	CE
----------------	----

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.000 cm
Package 1 Width	8.000 cm
Package 1 Length	8.000 cm
Package 1 Weight	89.000 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	9.000 cm
Package 2 Width	18.500 cm
Package 2 Length	27.500 cm
Package 2 Weight	971.000 g
Unit Type Of Package 3	S03
Number Of Units In Package 3	60
Package 3 Height	30.000 cm
Package 3 Width	30.000 cm
Package 3 Length	40.000 cm
Package 3 Weight	6.192 kg

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

## Well-being performance

<div><div>✓</div><div>Reach Free Of Svhc</div></div>	
<div><div>✓</div><div>Toxic Heavy Metal Free</div></div>	
<div><div>✓</div><div>Mercury Free</div></div>	
<div><div>✓</div><div>Rohs Exemption Information</div></div>	Yes
Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations