

Product data sheet

Specifications



Asfora, TV-SAT individual socket, 1dB, anthracite

EPH3400471

⚠ Discontinued on: Jun 30, 2023

⚠ Discontinued

Main

| | |
|--------------------------------------|-----------------------------------|
| Range | Asfora |
| Product Or Component Type | TV/SAT socket |
| Device Presentation | Mechanism with fixing frame |
| Tv Socket Type | Individual socket |
| Wiring Device Additional Information | For parallel distribution systems |
| Type Of Packing | Flow-pack |

Complementary

| | |
|-------------------------|--|
| Device Mounting | Flush |
| Fixing Mode | Claws51...80 mm |
| Socket Number | 2 |
| Tv Connector | Male IEC 9.52 mm |
| Sat Connector | F type |
| Attenuation | 1 dB |
| Colour Tint | Anthracite |
| Surface Finish | Painted |
| Material | ABS (acrylonitrile butadiene-styrene): central plate |
| Dc Current Flow | In SAT socket |
| Number Per Line | 1 |
| Connections - Terminals | Screwless terminals |
| Conductor Material | Copper |
| Height | 71 mm |
| Width | 71 mm |
| Depth | 42 mm |
| Projecting Depth | 13 mm |
| Net Weight | 0.105 kg |
| Ip Degree Of Protection | IP20 |

Environment

| | |
|----------------|----|
| Quality Labels | CE |
|----------------|----|

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Packing Units

| | |
|------------------------------|----------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 3.5 cm |
| Package 1 Width | 6.5 cm |
| Package 1 Length | 7 cm |
| Package 1 Weight | 83 g |
| Unit Type Of Package 2 | BB1 |
| Number Of Units In Package 2 | 10 |
| Package 2 Height | 9.5 cm |
| Package 2 Width | 18.5 cm |
| Package 2 Length | 27.5 cm |
| Package 2 Weight | 905 g |
| Unit Type Of Package 3 | S03 |
| Number Of Units In Package 3 | 60 |
| Package 3 Height | 30 cm |
| Package 3 Width | 30 cm |
| Package 3 Length | 40 cm |
| Package 3 Weight | 5.856 kg |

Sustainability




Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

Well-being performance

| | | |
|---|----------------------------|---|
|  | Toxic Heavy Metal Free | |
|  | Mercury Free | |
|  | Rohs Exemption Information | Yes |
| <hr/> | | |
| Eu Rohs Directive | | Compliant |
| | | EU RoHS Declaration |
| <hr/> | | |
| China Rohs Regulation | | China RoHS declaration |
| | | Pro-active China RoHS declaration (out of China RoHS legal scope) |
| <hr/> | | |