

# Product data sheet

Specifications

## Ultra - minitrunking - 12 x 7 mm - self-adhesive - PVC - white - 2 m



ETK12407

### Main

Range	Ultra
Product Or Component Type	Mini trunking
Device Application	Cable distribution
Quantity Per Set	154 m
Market Segment	Residential Small commercial

### Complementary

Trunking Material	Plastic
Compartment Partitioning	1 compartment
Trunking Dimension	12 x 7 mm
Fixing Mode	Pre-punched fixing hole 230 mm Power cable: screw-fixed Low voltage cable: adhesive tape
Material	PVC (polyvinyl chloride)
Length	2000 mm
Height	12 mm
Width	7 mm

### Environment

Ip Degree Of Protection	IP40
Ik Degree Of Protection	IK07
Ambient Air Temperature For Operation	-5...60 °C
Product Certifications	low voltage directive 2006/95/EC
Standards	EN 50085-1:2005 EN 50085-2-1:2006

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.0 cm
Package 1 Width	1.5 cm
Package 1 Length	200.0 cm
Package 1 Weight	255.0 g

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Unit Type Of Package 2	BB1
Number Of Units In Package 2	154
Package 2 Height	6.5 cm
Package 2 Width	15.0 cm
Package 2 Length	200.0 cm
Package 2 Weight	19.674 kg

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Circularity Profile	No need of specific recycling operations