

Product data sheet

Specifications



Pieno - 2 x 2.1A USB Charger - White

E8232USB_WE

Main

Product Or Component Type	USB charger
Fixing Mode	Screw

Complementary

Device Mounting	Flush
Device Presentation	Mechanism
Colour Tint	White
Surface Finish	Glossy
Surface Treatment	Untreated
Number Of Modules	2 modules 46 x 36.7 x 21.7 mm
Condition Of Use	Room temperature
Ambient Air Temperature For Storage	-5...60 °C
Relative Humidity	10...90 %
[Ue] Rated Operational Voltage	100/240 V AC 50/60 Hz
Integrated Connection Type	2 USB port 5 V DC, maximum load current: 2.1 A
Material	PA (polyamide) 6: housing Silicone rubber: cover PC (polycarbonate): grid plate
Shape Of Screw Head	Cross
Number Of Terminals	2 screw terminals
Clamping Connection Capacity	2.5 mm² for stranded cable(s) 2.5 mm² for flexible cable(s) 2.5 mm² for rigid cable(s) 1.5 mm² for stranded cable(s) 1.5 mm² for flexible cable(s) 1.5 mm² for rigid cable(s)
Wire Stripping Length	6 mm
Product Compatibility	Power bank Samsung HW Apple Major smart phone and tablet XiaoMi HTC
Standards	CNS 14336 MS IEC 60950-1 GB 4943.1 IEC 60950-1 CNS 13438

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Height	87 mm
Width	87 mm
Depth	39 mm
Embedding Depth	29.3 mm
Net Weight	0.1107 kg

Environment

Product Certifications	IEC CCC
Ip Degree Of Protection	IP20
Environmental Characteristic	Liquid soap Alcohol

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.8 cm
Package 1 Width	8.8 cm
Package 1 Length	8.8 cm
Package 1 Weight	117.0 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	8
Package 2 Height	9.5 cm
Package 2 Width	15 cm
Package 2 Length	19 cm
Package 2 Weight	936 g
Unit Type Of Package 3	CAR
Number Of Units In Package 3	80
Package 3 Height	21 cm
Package 3 Width	31 cm
Package 3 Length	50 cm
Package 3 Weight	9.36 kg

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information