

Product data sheet

Specifications



Ultra - front cover - 120 mm - PVC - white

ETK151501

⚠ Discontinued on: Apr 15, 2024

⚠ Discontinued

Main

Range Of Product	Ultra
Product Or Component Type	Front cover
Colour Tint	White (RAL 9010)
Quantity Per Set	Set of 8

Complementary

Trunking Dimension	151 x 50 mm
Trunking Material	Plastic
Fixing Mode	Snap-fitted
Material	PVC (polyvinyl chloride)
Length	2000 mm
Height	119 mm
Width	9 mm

Environment

Standards	EN 50085-1:2005 EN 50085-2-1:2006
Ambient Air Temperature For Operation	-25...60 °C
Ip Degree Of Protection	IP40
Ik Degree Of Protection	IK07

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.93 cm
Package 1 Width	11.9 cm
Package 1 Length	200 cm
Package 1 Weight	100 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	16
Package 2 Height	6.2 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 2 Width	13.9 cm
Package 2 Length	204 cm
Package 2 Weight	2.6 kg
Unit Type Of Package 3	PAL
Number Of Units In Package 3	1024
Package 3 Height	64.6 cm
Package 3 Width	205 cm
Package 3 Length	120 cm
Package 3 Weight	114.4 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Circularity Profile	No need of specific recycling operations