


Product data sheet

Specifications



Switch, AvatarOn, complete product, wine gold

E8333SRY800ZB_WG

Main

| | |
|----------------------------|------------------------|
| Product Brand | Schneider Electric |
| Range | AvatarOn |
| Product Or Component Type | Connected switch |
| Concentrator Compatibility | Wiser hub generation 1 |
| Mobile App Name | Wiser by SE |
| Number Of Rocker | 3 |

Complementary

| | |
|--------------------------------|---|
| Technology Type | Electronic |
| Device Presentation | Complete product |
| Load Type | Incandescent lamp: Halogen lamp: Fluorescent lamp: LED lamp: Exhaust fan: |
| Colour Tint | Wine gold |
| [Ue] Rated Operational Voltage | 200...240 V AC 50/60 Hz 4.04 A 100...120 V AC 50/60 Hz 4.44 A |
| Rated Power In W | 800 W |
| Local Signalling | Status indication: LED (white/blue) Programmable: LED (green/red/orange) |
| Communication Network Type | Wireless Zigbee (2.4 GHz) at < 50 m |
| Connections - Terminals | Brass terminal, 1...2.5 mm ² (AWG 18...AWG 13) solid Brass terminal, 1 x 2.5 mm ² Brass terminal, 2 x 1.5 mm ² |
| Device Mounting | Flush |
| Embedding Depth | 28 mm |
| Depth | 38 mm |
| Width | 86 mm |
| Height | 86 mm |
| Standards | EN 60669-2-5 IEC 60669-2-5 CE |
| Product Certifications | Zigbee 3.0 |

Environment

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

| | |
|---------------------------------------|-------------|
| Ambient Air Temperature For Operation | -10...45 °C |
| Relative Humidity | 10...95 % |
| Ip Degree Of Protection | IP20 |
| Operating Altitude | <= 2000 m |
| Environmental Characteristic | Indoor use |

Packing Units

| | |
|------------------------------|-----------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 5.5 cm |
| Package 1 Width | 9.5 cm |
| Package 1 Length | 12.5 cm |
| Package 1 Weight | 195.0 g |
| Unit Type Of Package 2 | S02 |
| Number Of Units In Package 2 | 20 |
| Package 2 Height | 15.0 cm |
| Package 2 Width | 30.0 cm |
| Package 2 Length | 40.0 cm |
| Package 2 Weight | 4.42 kg |
| Unit Type Of Package 3 | P06 |
| Number Of Units In Package 3 | 480 |
| Package 3 Height | 105.0 cm |
| Package 3 Width | 60.0 cm |
| Package 3 Length | 80.0 cm |
| Package 3 Weight | 115.96 kg |

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation [REACH Declaration](#)

Eu Rohs Directive Compliant with Exemptions

China Rohs Regulation [China RoHS declaration](#)

Environmental Disclosure [Product Environmental Profile](#)

Circularity Profile [End of Life Information](#)