

Product data sheet

Specifications



Socket-outlet, AvatarOn, complete product, 3P folded terminal polar white

E83426_15_WE_C5

Main

Product Or Component Type	Socket-outlet
Device Presentation	Complete product
Device Application	Power supply
Load Type	No inductive load
Colour Tint	White
Outlet Poles Configuration	3P
Outlet Standard	China

Complementary

Rated Current	15 A at 250 V AC 50 Hz
Socket Number	1
Socket-Outlet Type	Shuttered
Clamping Connection Capacity	1 x 4...2 x 4 mm ² for solid cable(s) 1 x 4...2 x 4 mm ² for stranded cable(s) 1 x 2.5...3 x 2.5 mm ² for solid cable(s) 1 x 2.5...3 x 2.5 mm ² for stranded cable(s)
Connections - Terminals	Folded terminal
Material	Polycarbonate grid plate Polycarbonate surround
Device Mounting	Surface
Width	86 mm
Height	86 mm
Depth	32.6 mm

Environment

Ip Degree Of Protection	IP20
Maximum Ambient Air Temperature For Operation	45 °C
Ambient Air Temperature For Storage	-5...60 °C
Relative Humidity	0...95 %
Environmental Characteristic	UV resistant
Standards	BS 546 SS 472 MS 1577
Product Certifications	SIRIM

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.3 cm
Package 1 Width	8.6 cm
Package 1 Length	8.6 cm
Package 1 Weight	81.0 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	9.5 cm
Package 2 Width	19.0 cm
Package 2 Length	19.5 cm
Package 2 Weight	982.0 g
Unit Type Of Package 3	CAR
Number Of Units In Package 3	60
Package 3 Height	21.0 cm
Package 3 Width	30.0 cm
Package 3 Length	39.5 cm
Package 3 Weight	5894.0 g

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations