

Product data sheet

Specifications



Ultra - installation trunking - 101 x 34 mm - plastic - white - 2 m

ETK10134E

Main

| | |
|---------------------------|-----------------------|
| Range | Ultra |
| Product Or Component Type | Installation trunking |
| Device Application | Cable distribution |
| Quantity Per Set | 24 m |
| Type Of Packing | Protective foil |

Complementary

| | |
|--------------------------|---|
| Compartment Partitioning | 1 compartment |
| Trunking Dimension | 101 x 34 mm |
| Device Composition | Trunking base Front cover |
| Trunking Material | Plastic |
| Front Opening Size | 75 mm |
| Fixing Mode | Screw-fixed Pre-punched fixing hole 230 mm |
| Material | PVC (polyvinyl chloride) |
| Length | 2000 mm |
| Height | 101 mm |
| Width | 34 mm |

Environment

| | |
|---------------------------------------|--------------------------------------|
| Ambient Air Temperature For Operation | -5...60 °C |
| Ip Degree Of Protection | IP40 |
| Ik Degree Of Protection | IK07 |
| Standards | EN 50085-1:2005 EN 50085-2-1:2006 |

Packing Units

| | |
|------------------------------|----------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 4.0 cm |
| Package 1 Width | 10.0 cm |
| Package 1 Length | 200.0 cm |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

| | |
|------------------------------|-----------|
| Package 1 Weight | 941.0 g |
| Unit Type Of Package 2 | BB1 |
| Number Of Units In Package 2 | 24 |
| Package 2 Height | 13.0 cm |
| Package 2 Width | 26.5 cm |
| Package 2 Length | 200.0 cm |
| Package 2 Weight | 22.617 kg |

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



RoHS/REACH

Well-being performance

| | | |
|---|----------------------------|-----|
| ✓ | Reach Free Of Svhc | |
| ✓ | Toxic Heavy Metal Free | |
| ✓ | Mercury Free | |
| ✓ | Rohs Exemption Information | Yes |

Certifications & Standards

| | |
|-----------------------|---|
| Reach Regulation | REACH Declaration |
| Eu Rohs Directive | Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration |
| China Rohs Regulation | China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope) |
| Circularity Profile | No need of specific recycling operations |