

Product data sheet

Specifications

Ultra - cable retainer - 101 x 34/50 mm - ABS - white



ETK10171E

Main

Range Of Product	Ultra
Product Or Component Type	Cable retainer
Colour Tint	White (RAL 9010)
Quantity Per Set	Set of 10

Complementary

Trunking Dimension	101 x 50 mm 101 x 34 mm
Trunking Material	Plastic
Fixing Mode	Snap-fitted
Material	PC/ABS
Height	9 mm
Width	81 mm
Depth	30 mm

Environment

Standards	EN 50085-1:2005 EN 50085-2-1:2006
Ambient Air Temperature For Operation	-25...60 °C
Ip Degree Of Protection	IP40
Ik Degree Of Protection	IK07

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1 cm
Package 1 Width	3 cm
Package 1 Length	8 cm
Package 1 Weight	7 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	5.5 cm
Package 2 Width	8 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 2 Length	9.5 cm
Package 2 Weight	90 g
Unit Type Of Package 3	S02
Number Of Units In Package 3	240
Package 3 Height	15 cm
Package 3 Width	30 cm
Package 3 Length	40 cm
Package 3 Weight	2.435 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Circularity Profile	No need of specific recycling operations