

Product data sheet

Specifications



Ultimate - Switched Socket 2 USB charger - 2 gang - 13A - polished - black

GGBGU34202USBBPB

⚠ Discontinued on: Jun 30, 2023

⚠ Discontinued

Main

Range	Ultimate
Product Or Component Type	Switched socket with USB charger
Device Presentation	Complete product
Colour Tint	Front plate: black
Surface Finish	Polished
Connections - Terminals	Screw terminals
Switch Function	1-pole

Complementary

Device Mounting	Surface Flush
Integrated Connection Type	2 USB port 5 V DC 2.1 A 2 socket-outlet 250 V AC 13 A 50/60 Hz
Actuator	Rocker
Number Of Gangs	2 gangs
Pilot Light	without LED
Fixing Mode	2 screw: M3.5 26 mm 2 screw: M3.5 32 mm
Clamping Connection Capacity	2 x 6 mm ² for solid cable(s) 3 x 4 mm ² for solid cable(s) 5 x 2.5 mm ² for solid cable(s) 3 x 4 mm ² for stranded cable(s) 5 x 2.5 mm ² for stranded cable(s)
Material	Steel
Product Compatibility	Mobile/tablet Apple Mobile/tablet Samsung Mobile/tablet LG Mobile/tablet Blackberry Mobile/tablet HTC Mobile/tablet Sony Mobile/tablet Huawei Technologies
Directives	2006/95/EC - low voltage directive 2004/108/EC - electromagnetic compatibility
Quality Labels	CE
Quantity Per Set	Set of 1
Type Of Packing	Bag
Type Of Installation	Indoor

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Depth	35 mm
Width	147.5 mm
Height	87.5 mm
Net Weight	0.29 kg

Environment

Ip Degree Of Protection	IP20
Standards	BS 1363-2

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4 cm
Package 1 Width	9.7 cm
Package 1 Length	15.4 cm
Package 1 Weight	338 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	50
Package 2 Height	18 cm
Package 2 Width	43 cm
Package 2 Length	50.5 cm
Package 2 Weight	17.6 kg
Unit Type Of Package 3	PAM
Number Of Units In Package 3	1000
Package 3 Height	106.5 cm
Package 3 Width	100 cm
Package 3 Length	120 cm
Package 3 Weight	372 kg

Sustainability


Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

Well-being performance

<div></div> <div>Rohs Exemption Information</div> <div>Yes</div>	
<hr/>	
Reach Regulation	REACH Declaration
<hr/>	
Eu Rohs Directive	Compliant
	EU RoHS Declaration
<hr/>	
China Rohs Regulation	China RoHS declaration
<hr/>	