

# Product data sheet

Specifications



## 4G cellular modem, EVlink

EVP3MM

### Main

Range	EVlink
Product Or Component Type	4G modem
Colour	Blue

### Complementary

Range Compatibility	EVlink EVlink parking charging station EVlink EVlink Smart Wallbox charging station EVlink EVlink City charging station
Kit Composition	1 modem 1 non fused power cord 1 fixing plate(s) 2 DIN rail mounting clip 2 screw antenna (to be ordered separately)
Transmission Rate	150 Mbps for downlink 50 Mbps for uplink
[Us] Rated Supply Voltage	7...32 V DC
Mounting Mode	By clips By screws
Integrated Connection Type	Micro SIM (3FF) card slot 1.8 V or 3 V RS232 - DE-9 RJ45 - 10/100BASE-T
Width	76 mm
Height	29 mm
Depth	106 mm
Net Weight	0.231 kg

### Environment

Ambient Air Temperature For Operation	-40...85 °C
Ambient Air Temperature For Storage	-40...85 °C
Relative Humidity	15...93 % non-condensing
Product Certifications	RED EN/IEC 60950-1

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Height	9.2 cm
Package 1 Width	17.7 cm
Package 1 Length	26.0 cm
Package 1 Weight	499.0 g
Unit Type Of Package 2	S04
Number Of Units In Package 2	12
Package 2 Height	30.0 cm
Package 2 Width	40.0 cm
Package 2 Length	60.0 cm
Package 2 Weight	6.645 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	96
Package 3 Height	75.0 cm
Package 3 Width	80.0 cm
Package 3 Length	120.0 cm
Package 3 Weight	65.624 kg

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

## Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes
Reach Regulation	REACH Declaration	
Eu Rohs Directive	Compliant	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)	