

Product data sheet

Specifications



Lisse White moulded - switched socket non-standard earth - 13 A - 230 V - 1 gang

GGBL3050NS

Main

Range	Lisse
Aesthetic Name	White moulded
Product Or Component Type	Switched socket
Device Presentation	Complete product
Outlet Standard	British
Colour Tint	Matt white
Socket Additional Information	T-shaped earth pin
Quantity Per Set	Set of 10
Type Of Packing	Carton

Complementary

Switch Function	1-pole
Rated Current	13 A at 250 V AC 50 Hz
Actuator	Rocker
Number Of Gangs	1 gang
Pilot Light	without LED
Fixing Mode	By screws Concealed screws
Connections - Terminals	Screw terminals
Material	Urea (carbamide)
Type Of Installation	Indoor
Depth	33 mm
Width	87 mm
Height	87 mm
Net Weight	0.09 kg

Environment

Standards	BS 1363-2
Ip Degree Of Protection	IP20

Packing Units

Unit Type Of Package 1	PCE
------------------------	-----

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Number Of Units In Package 1	1
Package 1 Height	3 cm
Package 1 Width	8.7 cm
Package 1 Length	8.7 cm
Package 1 Weight	93 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	9.5 cm
Package 2 Width	15.5 cm
Package 2 Length	18.5 cm
Package 2 Weight	1.03 kg
Unit Type Of Package 3	CAR
Number Of Units In Package 3	200
Package 3 Height	33 cm
Package 3 Width	38.5 cm
Package 3 Length	49.5 cm
Package 3 Weight	21.39 kg

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



RoHS/REACH

Well-being performance

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Circularity Profile	End of Life Information