

# Product data sheet

Specifications



## Lisse - universal dimmer - 4 gangs - 2 way - 250W/VA

GGBL6042CS

### Main

Range	Lisse
Aesthetic Name	White moulded
Product Or Component Type	Dimmer
Device Presentation	Complete product
Load Type	230 V AC halogen lamp Incandescent lamp: 250 W
Colour Tint	White matt
Quantity Per Set	Set of 1

### Complementary

Device Mounting	Wall mounted
Dimmer Application	Resistive load Inductive load
[Ue] Rated Operational Voltage	230 V AC 50 Hz
Number Of Gangs	4 gangs
Material	Urea (carbamide)
Connections - Terminals	Screw terminals
Fixing Mode	By screws M3.5 x 25 mm
Type Of Packing	Bag
Height	87 mm
Width	149 mm
Depth	43.6 mm
Net Weight	0.204 kg

### Environment

Standards	BS EN 60669-2-1
Ip Degree Of Protection	IP20

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.4 cm
Package 1 Width	8.7 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Length	14.9 cm
Package 1 Weight	272 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	5
Package 2 Height	9.8 cm
Package 2 Width	15.5 cm
Package 2 Length	23.2 cm
Package 2 Weight	1.42 kg
Unit Type Of Package 3	CAR
Number Of Units In Package 3	50
Package 3 Height	17 cm
Package 3 Width	48 cm
Package 3 Length	51 cm
Package 3 Weight	14.94 kg

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information   [Yes](#)

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations