

# Product data sheet

Specifications



Switched socket, Ultimate  
Screwless flat plate, 1P, screw  
terminal, IP20, stainless steel

GU3410BSS

## Main

Aesthetic Name	Screwless flat plate
Product Or Component Type	Switched socket
Rated Current	13 A at 230 V AC 50 Hz
Fixing Mode	By screws M3.5 x 30 mm
Colour Tint	Stainless steel

## Complementary

Device Presentation	Complete product
Outlet Poles Configuration	1P
Outlet Standard Description	3 pins
Outlet Standard	British
Actuator	Rocker
Number Of Gangs	1 gang
Earth Circuit	Standard earth
Pilot Light	Without neon indicator
Device Mounting	Wall mounted
Connections - Terminals	Screw terminal
Material	Steel
Quantity Per Set	Set of 1
Height	88 mm
Width	88 mm
Depth	30 mm
Socket Number	2

## Environment

Ip Degree Of Protection	IP20
Standards	BS 1363

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Width	9.5 cm
Package 1 Length	9.5 cm
Package 1 Weight	206.9 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	100
Package 2 Height	21 cm
Package 2 Width	42 cm
Package 2 Length	50 cm
Package 2 Weight	21.304 kg
Unit Type Of Package 3	PAM
Number Of Units In Package 3	1600
Package 3 Height	100.5 cm
Package 3 Width	100 cm
Package 3 Length	120 cm
Package 3 Weight	360.864 kg

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

## Well-being performance

 Rohs Exemption Information	Yes
<hr/>	
Reach Regulation	<a href="#">REACH Declaration</a>
<hr/>	
Eu Rohs Directive	Compliant with Exemptions
<hr/>	
China Rohs Regulation	<a href="#">China RoHS declaration</a>
<hr/>	