

Product data sheet

Specifications



Switched socket, Ultimate
Screwless flat plate, 2P, screw
terminal, IP20, black nickel

GU3410DBBN

Main

Range	Ultimate
Device Application	Power supply
Aesthetic Name	Screwless flat plate
Product Or Component Type	Switched socket
Rated Current	13 A at 230 V AC 50 Hz
Fixing Mode	By screws M3.5 x 30 mm
Colour Tint	Black nickel

Complementary

Device Presentation	Complete product
Outlet Poles Configuration	2P
Outlet Standard Description	3 pins
Outlet Standard	British
Actuator	Rocker
Number Of Gangs	1 gang
Earth Circuit	Standard earth
Pilot Light	Without neon indicator
Device Mounting	Wall mounted
Connections - Terminals	Screw terminal
Material	Stainless steel
Quantity Per Set	Set of 1
Height	88 mm
Width	88 mm
Depth	30 mm
Socket Number	1
Mounting Mode	Horizontal

Environment

Ip Degree Of Protection	IP20
Standards	BS

Packing Units

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.000 cm
Package 1 Width	9.500 cm
Package 1 Length	9.600 cm
Package 1 Weight	213.700 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	100
Package 2 Height	21.500 cm
Package 2 Width	42.000 cm
Package 2 Length	50.000 cm
Package 2 Weight	21.931 kg
Unit Type Of Package 3	PAM
Number Of Units In Package 3	1600
Package 3 Height	102.500 cm
Package 3 Width	120.000 cm
Package 3 Length	100.000 cm
Package 3 Weight	370.888 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

 Mercury Free	
 Rohs Exemption Information	Yes
Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration