

Product data sheet

Specifications



Lisse - USB Charger 1gang 2 module Satin Brass with Black Interior

GGBL70042BSBS

Main

Range	Lisse
Aesthetic Name	Screwless deco
Product Or Component Type	USB charger
Provided Equipment	USB charger
Quantity Per Set	Set of 1
Type Of Packing	Bag
Colour Tint	Interior: black Cover plate: polished chrome
Surface Finish	Brushed finish

Complementary

Number Of Modules	2 modules
Number Of Gangs	1 gang
Device Mounting	Wall mounted
[Ue] Rated Operational Voltage	250 V AC 50 Hz
Output Voltage	5 V DC 3.1 A
Number Of Terminals	2 terminal connectors
Material	Stainless steel
Protection Type	Overheating protection
Fixing Mode	Concealed screws
Height	87 mm
Width	87 mm
Depth	34 mm
Type Of Installation	Indoor

Environment

Ambient Air Temperature For Operation	0...45 °C
Ambient Air Temperature For Storage	0...60 °C
Standards	BS EN 60950
Product Certifications	EN 60950
Electrical Insulation Class	Class II
Ip Degree Of Protection	IP20

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.300 cm
Package 1 Width	8.700 cm
Package 1 Length	8.700 cm
Package 1 Weight	169.900 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	5
Package 2 Height	10.000 cm
Package 2 Width	10.200 cm
Package 2 Length	20.500 cm
Package 2 Weight	925.000 g
Unit Type Of Package 3	CAR
Number Of Units In Package 3	100
Package 3 Height	22.000 cm
Package 3 Width	43.000 cm
Package 3 Length	53.000 cm
Package 3 Weight	19.209 kg

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations