

Product data sheet

Specifications



Ultimate Flat plate - switched socket - 1 gang - brass

GU3210BPB

⚠ Discontinued on: Mar 31, 2023

⚠ Discontinued

Main

Range	Ultimate
Device Application	Power supply
Aesthetic Name	Flat plate
Product Or Component Type	Switched socket
Rated Current	13 A at 230 V AC 50 Hz
Fixing Mode	By screws M3.5 x 30 mm
Colour Tint	Brass

Complementary

Device Presentation	Complete product
Outlet Poles Configuration	1P
Outlet Standard Description	3 pins
Outlet Standard	British
Actuator	Rocker
Number Of Gangs	1 gang
Earth Circuit	Standard earth
Pilot Light	Without neon indicator
Device Mounting	Wall mounted
Connections - Terminals	Screw terminal
Material	Stainless steel
Quantity Per Set	Set of 1
Height	88 mm
Width	88 mm
Depth	30 mm
Socket Number	1
Mounting Mode	Horizontal

Environment

Ip Degree Of Protection	IP20
Standards	BS

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4 cm
Package 1 Width	9.5 cm
Package 1 Length	9.7 cm
Package 1 Weight	176 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	100
Package 2 Height	21.5 cm
Package 2 Width	42.5 cm
Package 2 Length	50 cm
Package 2 Weight	18.18 kg
Unit Type Of Package 3	PAM
Number Of Units In Package 3	1600
Package 3 Height	102.5 cm
Package 3 Width	100 cm
Package 3 Length	120 cm
Package 3 Weight	310.88 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

Well-being performance

 Mercury Free	
 Rohs Exemption Information	Yes
Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration