

# Product data sheet

Specifications

## Linergy FT, Comb busbar, 63A, 3 tap-offs, 54mm pitch



GV2G354

### Main

Range	Linergy
Product Name	FT
Device Short Name	GV2G
Product Or Component Type	Comb busbar
Accessory / Separate Part Category	Connection accessory
Poles Description	3P
Range Compatibility	TeSys Deca TeSys GV2 TeSys K TeSys U
Number Of Tap-Offs	3
[Ith] Conventional Free Air Thermal Current	63 A
Connection Pitch	54 mm

### Complementary

Mounting Location	On terminal
[U] Rated Insulation Voltage	690 V
Length	152 mm
Net Weight	0.06 kg

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1 cm
Package 1 Width	3.1 cm
Package 1 Length	15.1 cm
Package 1 Weight	64 g
Unit Type Of Package 2	S01
Number Of Units In Package 2	70
Package 2 Height	15 cm
Package 2 Width	15 cm
Package 2 Length	40 cm
Package 2 Weight	4.589 kg

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Unit Type Of Package 3	P06
Number Of Units In Package 3	2240
Package 3 Height	77 cm
Package 3 Width	80 cm
Package 3 Length	60 cm
Package 3 Weight	159.06 kg

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free


✓ Rohs Exemption Information   Yes

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End of Life Information</a>

Dimensions Drawings

Sets of Busbars GV2G345 and GV2G354



	I
GV2G345 (3 x 45 mm)	134
GV2G354 (3 x 54 mm)	152