

Product data sheet

Specifications

Linergy FT, Comb busbar, 63A, 2 tap-offs, 45mm pitch



GV2G245

Main

Range	Linergy
Product Name	FT
Device Short Name	GV2G
Product Or Component Type	Comb busbar
Accessory / Separate Part Category	Connection accessory
Poles Description	3P
Range Compatibility	TeSys GV2 TeSys Deca TeSys U
Number Of Tap-Offs	2
[Ith] Conventional Free Air Thermal Current	63 A
Connection Pitch	45 mm

Complementary

Mounting Location	On terminal
[Ui] Rated Insulation Voltage	690 V
Length	89 mm
Net Weight	0.036 kg

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2 cm
Package 1 Width	4 cm
Package 1 Length	9.5 cm
Package 1 Weight	37 g
Unit Type Of Package 2	S01
Number Of Units In Package 2	100
Package 2 Height	15 cm
Package 2 Width	15 cm
Package 2 Length	40 cm
Package 2 Weight	3.862 kg

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Unit Type Of Package 3	P06
Number Of Units In Package 3	3200
Package 3 Height	77 cm
Package 3 Width	80 cm
Package 3 Length	60 cm
Package 3 Weight	130.9 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free


✓ Rohs Exemption Information Yes

Certifications & Standards


Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information

Dimensions Drawings

Sets of Busbars GV2G... with Terminal Block GV1G09



Sets of Busbars GV2G245, GV2G254, GV2GR272



	I
GV2G245 (2 x 45 mm)	89
GV2G254 (2 x 54 mm)	98
GV2G272 (2 x 72 mm)	116