

Product data sheet

Specifications



Mureva U56 - j box - 10 grommets - without terminal - russian label - polarwhite

IMT34349

⚠ Discontinued on: Apr 15, 2024

⚠ Discontinued

Main

Range Of Product	Mureva
Product Name	Mureva BOX
Device Short Name	U56
Product Or Component Type	Junction box
Device Application	Cable installation
Colour Tint	White (RAL 9003)
Quantity Per Set	Set of 2

Complementary

Device Mounting	Surface
Fixing Mode	By screw: body housing
Base Dimension	92 x 45 x 65 mm
Cable Entry	Grommets
Cable Entry Number	10 diameter: 14 mm
Material	ABS (acrylonitrile butadiene-styrene)
Height	87 mm
Width	87 mm
Depth	39 mm

Environment

Ambient Air Temperature For Operation	-25...60 °C
Ip Degree Of Protection	IP55
Standards	EN 60670-1
Product Certifications	DEMKO SEMKO FIMKO NEMKO

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.9 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Width	8.7 cm
Package 1 Length	8.7 cm
Package 1 Weight	75.0 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	150
Package 2 Height	45.5 cm
Package 2 Width	29.6 cm
Package 2 Length	40.3 cm
Package 2 Weight	16.26 kg

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations