

Product data sheet

Specifications



Multifix Modulo - apparatus box - 1module - 8 knock-outs - green - Ø65x4 mm

IMT35100

⚠ Discontinued on: Dec 31, 2023

⚠ Discontinued

Main

Range Of Product	Multifix
Product Name	Multifix Modulo
Product Or Component Type	Apparatus box
Quantity Per Set	Set of 200

Complementary

Device Mounting	Flush
Mounting Support	Brick
Number Of Gangs	1 gang
Cable Entry	2 knock-out for 10 mm 3 knock-out for 16 mm 3 knock-out for 20 mm
Colour Tint	Green (RAL 6001)
Material	PP (polypropylene) (untreated)
Distance Between Supports	60 mm
Diameter	65 mm
Internal Depth	44 mm
Length	81 mm
Width	71 mm
Depth	46 mm
Cable Cross Section	2.5 mm ²
Tube Diameter	0.84 mm
Sealing	Without

Environment

Standards	IEC 60670-1
Ambient Air Temperature For Operation	-25...60 °C
Ip Degree Of Protection	IP30

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Height	4.500 cm
Package 1 Width	7.000 cm
Package 1 Length	7.000 cm
Package 1 Weight	13.200 g
Unit Type Of Package 2	S04
Number Of Units In Package 2	200
Package 2 Height	30.000 cm
Package 2 Width	40.000 cm
Package 2 Length	60.000 cm
Package 2 Weight	3.114 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	3600
Package 3 Height	114.500 cm
Package 3 Width	80.000 cm
Package 3 Length	120.000 cm
Package 3 Weight	68.052 kg

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations