

Product data sheet

Specifications



Multifix TED - apparatus box - cast-in cover - single - 3 stubs - green

IMT36255

⚠ Discontinued on: Dec 17, 2020

⚠ Discontinued

Main

Range Of Product	Multifix
Product Name	Multifix TED
Device Short Name	TED-A13 IG
Product Or Component Type	Apparatus box
Device Application	Single board
Quantity Per Set	Set of 100

Complementary

Device Mounting	Flush
Device Composition	Cast-in cover With stubs located 13 mm from the front edge of the box
Mounting Support	Board
Number Of Stubs	3 - diameter: 16 mm
Number Of Gangs	1 gang
Colour Tint	Green
Material	PEHD (polyethylene high density) (untreated)
Distance Between Supports	60 mm
Diameter	74 mm
Internal Depth	46 mm
Length	120 mm
Width	50 mm
Depth	48 mm
Cable Cross Section	2.5 mm ²
Tube Diameter	16 mm
Sealing	With
Connections - Terminals	Snap-on

Environment

Standards	IEC 60670-1
Ambient Air Temperature For Operation	-25...60 °C
Ip Degree Of Protection	IP20

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5 cm
Package 1 Width	7 cm
Package 1 Length	12 cm
Package 1 Weight	54 g

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations