

# Product data sheet

Specifications



## Multifix TED - apparatus box - double - 3 stubs - red

IMT36256

### Main

Range Of Product	Multifix
Product Name	Multifix TED
Device Short Name	TED-A26
Product Or Component Type	Apparatus box
Device Application	Double board
Quantity Per Set	Set of 200

### Complementary

Device Mounting	Flush
Device Composition	With stubs located 26 mm from the front edge of the box
Mounting Support	Board
Number Of Stubs	3 - diameter: 16 mm
Number Of Gangs	1 gang
Colour Tint	Red
Material	PEHD (polyethylene high density) (untreated)
Distance Between Supports	60 mm
Diameter	74 mm
Internal Depth	46 mm
Length	120 mm
Width	78 mm
Depth	48 mm
Net Weight	0.05 kg
Cable Cross Section	2.5 mm²
Tube Diameter	16 mm
Sealing	Without
Connections - Terminals	Screwed

### Environment

Standards	IEC 60670-1
Ambient Air Temperature For Operation	-25...60 °C
Ip Degree Of Protection	IP20

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.700 cm
Package 1 Width	7.100 cm
Package 1 Length	11.800 cm
Package 1 Weight	58.000 g
Unit Type Of Package 2	P12
Number Of Units In Package 2	2400
Package 2 Height	80.000 cm
Package 2 Width	93.000 cm
Package 2 Length	120.000 cm
Package 2 Weight	165288.000 kg

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information   Yes

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations