

Product data sheet

Specifications



Mureva – IP65 junc box – 14 membranes - 87x87 mm – with strain relief - white

IMT35343

⚠ Discontinued on: Jun 30, 2023

⚠ Discontinued

Main

Range Of Product	Mureva
Product Or Component Type	Junction box
Device Application	Cable installation
Colour Tint	White (RAL 9003)
Quantity Per Set	Set of 5

Complementary

Device Mounting	Surface
Fixing Mode	By screws: body housing
Base Dimension	87 x 87 x 42 mm
Cable Entry	Grommets
Cable Entry Number	14 diameter: 19 mm
Material	PP (polypropylene)
Height	87 mm
Width	87 mm
Depth	42 mm
Net Weight	62 g

Environment

Ambient Air Temperature For Operation	-25...60 °C
Ip Degree Of Protection	IP65
Glow Wire Temp	650 °C
Standards	EN 60670
Product Certifications	DEMKO FIMKO NEMKO SEMKO

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.5 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Width	8.7 cm
Package 1 Length	8.7 cm
Package 1 Weight	67 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	5
Package 2 Height	8.7 cm
Package 2 Width	8.7 cm
Package 2 Length	22.2 cm
Package 2 Weight	335 g
Unit Type Of Package 3	S03
Number Of Units In Package 3	60
Package 3 Height	30 cm
Package 3 Width	30 cm
Package 3 Length	40 cm
Package 3 Weight	4.525 kg

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations