

Product data sheet

Specifications



Multifix Eco - Board fixing 70mm

IMT36226

Main

Range Of Product	Multifix
Range Compatibility	Multifix Eco
Product Or Component Type	Board fixing
Product Specific Application	For gluing/screw fixing of boxes between boards
Quantity Per Set	Set of 10

Complementary

Mounting Support	Beam - thickness: 70 mm
Colour Tint	Blue (NCS S 3050-R90B)
Material	PP (polypropylene) 10 % talcum
Length	30 mm
Width	70 mm
Depth	65 mm
Net Weight	0.013 kg

Environment

Ambient Air Temperature For Operation	-25...60 °C
Ip Degree Of Protection	IP20

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.200 cm
Package 1 Width	6.500 cm
Package 1 Length	6.900 cm
Package 1 Weight	8.000 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	100
Package 2 Height	31.600 cm
Package 2 Width	30.200 cm
Package 2 Length	39.200 cm
Package 2 Weight	1.692 kg

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Unit Type Of Package 3	P12
Number Of Units In Package 3	2400
Package 3 Height	80.000 cm
Package 3 Width	108.300 cm
Package 3 Length	120.000 cm
Package 3 Weight	60408.000 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations