

# Product data sheet

Specifications



## Multifix TED - apparatus box - spacing collar - single - 3 stubs - green

IMT36252

 **Discontinued on:** Sep 30, 2021

 **Discontinued**

### Main

Range Of Product	Multifix
Product Name	Multifix TED
Device Short Name	TED-A13R
Product Or Component Type	Apparatus box
Device Application	Single board
Quantity Per Set	Set of 100

### Complementary

Device Mounting	Flush
Device Composition	With stubs located 13 mm from the front edge of the box Spacing collar
Mounting Support	Board
Number Of Stubs	3 - diameter: 16 mm
Number Of Gangs	1 gang
Colour Tint	Green
Material	PEHD (polyethylene high density) (untreated)
Distance Between Supports	60 mm
Diameter	74 mm
Internal Depth	46 mm
Length	120 mm
Width	58 mm
Depth	58 mm
Net Weight	0.05 kg
Cable Cross Section	2.5 mm <sup>2</sup>
Tube Diameter	16 mm
Sealing	Without
Connections - Terminals	Screwed

### Environment

Standards	IEC 60670-1
Ambient Air Temperature For Operation	-25...60 °C

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Ip Degree Of Protection	IP20
-------------------------	------

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.7 cm
Package 1 Width	8.2 cm
Package 1 Length	11.9 cm
Package 1 Weight	66 g

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information   Yes

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations