

# Product data sheet

Specifications



## Socket-outlet, Unica System+, complete product Schuko IP44 grey

INS52101

### Main

Range	Unica
Product Type	Socket-outlet
Device Application	Power socket distribution
Cabling Installation System	Floor outlet box
Type Of Floor	Raised floor In-cavity floor Hollow core floor
Floor Box Shape	Round
Colour	Grey
Outlet Standard	Schuko

### Complementary

Device Presentation	Complete product
Product Compatibility	mounting boxes
Size	Housing: XS
Device Mounting	Floor mounted
Fixing Mode	By 2 screws
Function Available	Cover opening up to 180°
Product Material	Stainless steel brushed finish
Height	43 mm
Width	90 mm
Depth	90 mm

### Environment

Ik Degree Of Protection	IK08
Ip Degree Of Protection	IP44
Market Segment	Commercial Office School

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.800 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Width	9.500 cm
Package 1 Length	11.500 cm
Package 1 Weight	186.000 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	30
Package 2 Height	30.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	5.874 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	720
Package 3 Height	105.000 cm
Package 3 Width	80.000 cm
Package 3 Length	120.000 cm
Package 3 Weight	155.976 kg

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information   Yes

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations