

Product data sheet

Specifications



OptiLine 70 - installation trunking - 95x55 mm - PVC - polar white - 2000 mm

ISM11200P

 **Discontinued on:** Jun 30, 2023

 **Discontinued**

Main

| | |
|-----------------------------|------------------------|
| Range Of Product | OptiLine 70 |
| Cabling Installation System | Trunking |
| Product Or Component Type | Installation trunking |
| Colour Tint | Polar white (RAL 9003) |
| Quantity Per Set | 12 m |

Complementary

| | |
|--------------------------|--------------------------|
| Trunking Material | Plastic |
| Trunking Dimension | 95 x 55 mm |
| Compartment Partitioning | 1 compartment |
| Mounting Location | Internal |
| Fixing Mode | By screws |
| Front Opening Size | 70 mm |
| Material | PVC (polyvinyl chloride) |
| Length | 2000 mm |
| Height | 95 mm |
| Width | 55 mm |

Environment

| | |
|---------------------------------------|--|
| Standards | 73/23/EEC 93/68/EEC EN 50085-1:2005 EN 50085-2-1:2002 |
| Ambient Air Temperature For Operation | -25...60 °C |
| Ip Degree Of Protection | IP40 |
| Ik Degree Of Protection | IK07 |

Packing Units

| | |
|------------------------------|--------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 2 |
| Package 1 Height | 5.5 cm |
| Package 1 Width | 9.5 cm |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

| | |
|------------------------------|----------|
| Package 1 Length | 200.0 cm |
| Package 1 Weight | 1.98 kg |
| Unit Type Of Package 2 | BB1 |
| Number Of Units In Package 2 | 12 |
| Package 2 Height | 12.0 cm |
| Package 2 Width | 25.0 cm |
| Package 2 Length | 204.0 cm |
| Package 2 Weight | 12.13 kg |
| Unit Type Of Package 3 | PAL |
| Number Of Units In Package 3 | 192 |
| Package 3 Height | 62.0 cm |
| Package 3 Width | 120.0 cm |
| Package 3 Length | 210.0 cm |
| Package 3 Weight | 214.0 kg |

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

| | | |
|---|----------------------------|-----|
| ✓ | Reach Free Of Svhc | |
| ✓ | Toxic Heavy Metal Free | |
| ✓ | Mercury Free | |
| ✓ | Rohs Exemption Information | Yes |

Certifications & Standards

| | |
|--------------------------|---|
| Reach Regulation | REACH Declaration |
| Eu Rohs Directive | Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration |
| China Rohs Regulation | China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope) |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | No need of specific recycling operations |