

Product data sheet

Specifications



OptiLine 70 - internal corner - PC/ ABS - aluminium metallic

ISM11251

⚠ Discontinued on: Jun 30, 2023

⚠ Discontinued

Main

Range Of Product	OptiLine 70
Cabling Installation System	Trunking
Product Type	Internal corner
Colour	Aluminium metallic
Quantity Package 1 / Unit	Set of 1

Complementary

Trunking Material	Aluminium
Trunking Dimension	95 x 55 mm
Fixing Mode	Snap-fitted
Product Material	PC/ABS painted
Length	117 mm
Height	104 mm
Width	117 mm

Environment

Standards	73/23/EEC 93/68/EEC EN 50085-1:2005 EN 50085-1:2013/A1 EN 50085-2-1:2006 EN 50085-2-1:2011/A1 NF C 68-102
Operating Temperature	-25...60 °C
Ip Degree Of Protection	IP40
Ik Degree Of Protection	IK07

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	11.7 cm
Package 1 Width	10.4 cm
Package 1 Length	11.7 cm
Package 1 Weight	90.8 g

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Unit Type Of Package 2	BAG
Number Of Units In Package 2	10
Package 2 Height	30.0 cm
Package 2 Width	29.9 cm
Package 2 Length	39.8 cm
Package 2 Weight	1.401 kg
Unit Type Of Package 3	PAL
Number Of Units In Package 3	80
Package 3 Height	45.0 cm
Package 3 Width	80.0 cm
Package 3 Length	120.0 cm
Package 3 Weight	23.208 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency

Well-being performance

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
--------------------------	---------------------------------------------------------------------------------------------------

China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
------------------------------	-------------------------------------------------------------------------------------------------------------

Environmental Disclosure	Product Environmental Profile
---------------------------------	-----------------------------------------------

Circularity Profile	No need of specific recycling operations
----------------------------	------------------------------------------