

Product data sheet

Specifications



OptiLine - stop end 12 x 20 mm - PC/ABS aluminium metallic

ISM14154

 **Discontinued on:** Jun 30, 2023

 **Discontinued**

Main

Range	OptiLine
Cabling Installation System	Mini trunking
Product Type	Stop end
Trunking Type	Mini trunking
D_Range_Compatibility	OptiLine

Complementary

Trunking Material	Plastic
Colour Tint	Aluminium metallic
Trunking Dimension	12 x 20 mm
Fixing Mode	Snap-fitted
Surface Finish	Painted
Material	PC/ABS
Quantity Per Package	Set of 10
Operating Temperature	-15...60 °C
Length	13 mm
Height	22 mm
Width	15 mm

Environment

Standards	73/23/EEC EN 50085-1:2005 EN 50085-2-1:2006
Ip Degree Of Protection	IP40
Ik Degree Of Protection	IK06

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.2 cm
Package 1 Width	1.5 cm
Package 1 Length	2.1 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Weight	1.7 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	2.5 cm
Package 2 Width	7.0 cm
Package 2 Length	17.8 cm
Package 2 Weight	18.0 g
Unit Type Of Package 3	S01
Number Of Units In Package 3	500
Package 3 Height	15.0 cm
Package 3 Width	15.0 cm
Package 3 Length	40.0 cm
Package 3 Weight	1.004 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations