

# Product data sheet

Specifications



## OptiLine 50 - cable connector - GST 18i3 female

INS70010

⚠ Discontinued on: Jun 30, 2023

⚠ Discontinued

### Main

Range Of Product	OptiLine 50
Product Type	Cable connector
Additional Information	Unassembled
Colour	White
Quantity Package 1 / Unit	Set of 10

### Complementary

Interface	GST 18i3 female (3 poles)
Rating	16 A - 250 V
Product Material	PA (polyamide)
Connections - Terminals	Screw connection
Suitable For	0.75...2.5 mm², 6.5...10.5 mm, fine stranded 0.75...2.5 mm², 6.5...10.5 mm, rigid
Length	70 mm
Height	13 mm
Width	28 mm

### Environment

Operating Temperature	-5...40 °C
Ip Degree Of Protection	IP20

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.300 cm
Package 1 Width	2.800 cm
Package 1 Length	7.000 cm
Package 1 Weight	19 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	50
Package 2 Height	16.500 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 2 Width	20.500 cm
Package 2 Length	34.500 cm
Package 2 Weight	1.220 kg
Unit Type Of Package 3	S04
Number Of Units In Package 3	150
Package 3 Height	30.000 cm
Package 3 Width	40.000 cm
Package 3 Length	60.000 cm
Package 3 Weight	4.718 kg

## Contractual warranty

Warranty	18 months
----------	-----------

# Sustainability

**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.


[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

 Rohs Exemption Information   [Yes](#)

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations