

Product data sheet

Specifications



Stop end, OptiLine, for 25x60mm trunking, PC/ABS, white

ISM14604

Main

| | |
|-----------------------------|---------------|
| Range | OptiLine |
| Cabling Installation System | Mini trunking |
| Product Type | Stop end |
| Trunking Type | Mini trunking |
| D_Range_Compatibility | OptiLine |

Complementary

| | |
|-----------------------|------------------|
| Trunking Material | Plastic |
| Colour Tint | White (RAL 9010) |
| Trunking Dimension | 25 x 60 mm |
| Fixing Mode | Snap-fitted |
| Material | PC/ABS |
| Quantity Per Package | Set of 10 |
| Operating Temperature | -5...60 °C |
| Length | 62 mm |
| Height | 26 mm |
| Width | 17 mm |

Environment

| | |
|-------------------------|---------------------------------------------------|
| Standards | 73/23/EEC EN 50085-1:2005 EN 50085-2-1:2006 |
| Ip Degree Of Protection | IP40 |
| Ik Degree Of Protection | IK07 |

Packing Units

| | |
|------------------------------|----------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 1.600 cm |
| Package 1 Width | 2.600 cm |
| Package 1 Length | 6.100 cm |
| Package 1 Weight | 5.000 g |
| Unit Type Of Package 2 | P12 |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

| | |
|------------------------------|--------------|
| Number Of Units In Package 2 | 7200 |
| Package 2 Height | 60.000 cm |
| Package 2 Width | 80.000 cm |
| Package 2 Length | 120.000 cm |
| Package 2 Weight | 51456.000 kg |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Sustainable Packaging Transparency RoHS/REACH

Resource performance

✓ Sustainable Packaging

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

| | |
|--------------------------|-------------------------------------------------------------------------------------------------------------|
| Reach Regulation | REACH Declaration |
| Eu Rohs Directive | Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration |
| China Rohs Regulation | China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope) |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | No need of specific recycling operations |