

Product data sheet

Specifications



OptiLine 45 - wall/ceiling frame - PC/ABS - aluminium metallic

ISM10555

 **Discontinued on:** Jun 30, 2023

 **Discontinued**

Main

Range Of Product	OptiLine 45
Cabling Installation System	Trunking
Product Type	Wall/ceiling frame
Colour	Aluminium metallic
Quantity Package 1 / Unit	Set of 1

Complementary

Trunking Material	Aluminium
Trunking Dimension	185 x 55 mm
Fixing Mode	Snap-fitted
Product Material	PC/ABS painted
Length	22 mm
Height	240 mm
Width	82 mm

Environment

Standards	73/23/EEC 93/68/EEC EN 50085-1:2005 EN 50085-1:2013/A1 EN 50085-2-1:2006 EN 50085-2-1:2011/A1 NF C 68-102
Operating Temperature	-25...60 °C
Ip Degree Of Protection	IP30
Ik Degree Of Protection	IK07

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	24 cm
Package 1 Width	8.2 cm
Package 1 Length	2.2 cm
Package 1 Weight	45 g

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Unit Type Of Package 2	BAG
Number Of Units In Package 2	50
Package 2 Height	30 cm
Package 2 Width	29.9 cm
Package 2 Length	39.8 cm
Package 2 Weight	2.781 kg
Unit Type Of Package 3	PAL
Number Of Units In Package 3	400
Package 3 Height	45 cm
Package 3 Width	80 cm
Package 3 Length	120 cm
Package 3 Weight	34.248 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations