

Product data sheet

Specifications



OptiLine 70 - adaptor for Altira wiring device - 1 module - polar white

ISM15100P

⚠ Discontinued on: Jun 30, 2023

⚠ Discontinued

Main

Range Of Product	OptiLine 70
Cabling Installation System	Pole Trunking
Product Type	Adaptor
Trunking Material	Aluminium Plastic
Type Of Pole	Two-sided One-sided
Type Of Post	One-sided Two-sided
Type Of Service Box	Service box kit
Trunking Dimension	80 x 55 mm 185 x 55 mm 95 x 55 mm 120 x 55 mm 155 x 55 mm
Configuration	Empty
Suitable For	Altira wiring device
Pole/Post Surface Finish	Anodized
Pole Fixing Mode	Tension-mounted Free-standing

Complementary

Number Of Modules	1 module
Colour	Polar white (RAL 9003)
Fixing Mode	Snap-fitted
Product Material	PC/ABS
Quantity Package 1 / Unit	Set of 1
Length	71 mm
Height	73 mm
Width	35 mm

Environment

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Standards	73/23/EEC 93/68/EEC EN 50085-1:2005 EN 50085-2-1:2002
Operating Temperature	-25...60 °C
Ip Degree Of Protection	IP21

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.2 cm
Package 1 Width	7.2 cm
Package 1 Length	7.7 cm
Package 1 Weight	36.0 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	70
Package 2 Height	30.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	3.032 kg

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations