

Product data sheet

Specifications



OptiLine 70 - installation trunking - 120x55 mm - PVC - polar white - 2000 mm

ISM11300P

Main

Range Of Product	OptiLine 70
Cabling Installation System	Trunking
Product Or Component Type	Installation trunking
Colour Tint	Polar white (RAL 9003)
Quantity Per Set	12 m

Complementary

Trunking Material	Plastic
Trunking Dimension	120 x 55 mm
Compartment Partitioning	1 compartment
Fixing Mode	By screws
Front Opening Size	70 mm
Material	PVC (polyvinyl chloride)
Length	2000 mm
Height	120 mm
Width	55 mm

Environment

Standards	73/23/EEC 93/68/EEC EN 50085-1:2005 EN 50085-2-1:2002
Ambient Air Temperature For Operation	-25...60 °C
Ip Degree Of Protection	IP40
Ik Degree Of Protection	IK07

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	2
Package 1 Height	5.5 cm
Package 1 Width	12.0 cm
Package 1 Length	200.0 cm
Package 1 Weight	2.04 kg

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Unit Type Of Package 2	BB1
Number Of Units In Package 2	12
Package 2 Height	12.0 cm
Package 2 Width	25.0 cm
Package 2 Length	204.0 cm
Package 2 Weight	12.51 kg
Unit Type Of Package 3	PAL
Number Of Units In Package 3	156
Package 3 Height	62.0 cm
Package 3 Width	120.0 cm
Package 3 Length	210.0 cm
Package 3 Weight	183.0 kg

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations